

LESSMANN[®]
THE GERMAN BRUSH COMPANY**Tube brush Waved steel wire 0.15 mm, Brush Ø: 10mm****Order data**

Order number	577980 10
GTIN	4017359004265
Item class	57L

Description**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles. Bristles of waved wire, overall length 115 mm. Bristle length 80 mm long with crimped-on M6 threaded nipple.

Application:

For cleaning pipes, gratings, sleeves, heat exchangers, and cylinders. For use in machines (only clockwise rotation), use thread adapter No. 577990.

Technical description

Brush Ø D ₁	10 mm
Overall length L	115 mm
Brush material	Steel wire
Adapter	Threaded nipple
Bristle thickness	0.15 mm
Type of product	Tube brush

Accessories

Extension for tube brushes with M6 threaded nipple Thread M6	577993 M6
	577990 M6

M6 thread adapter, internal thread
Shank Ø 6 mm Thread
M6

Plastic handle for tube brushes with M6 threaded nipple
Thread M6

577995 M6