

**LESSMANN®**  
THE GERMAN BRUSH COMPANY
**Tube brush Waved steel wire 0.15 mm, Brush Ø: 16mm**

**Order data**

Order number	577980 16
GTIN	4017359004340
Item class	57L

**Description**
**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles. Bristles of waved wire, overall length 115 mm. Bristle length 80 mm long with crimped-on M6 threaded nipple.

**Application:**

For cleaning pipes, gratings, sleeves, heat exchangers, and cylinders. For use in machines (only clockwise rotation), use thread adapter No. 577990.

**Technical description**

Brush Ø D <sub>1</sub>	16 mm
Overall length L	115 mm
Brush material	Steel wire
Adapter	Threaded nipple
Bristle thickness	0.15 mm
Type of product	Tube brush

**Accessories**

Plastic handle for tube brushes with M6 threaded nipple Thread M6	577995 M6
	577990 M6

M6 thread adapter, internal thread Shank Ø 6 mm Thread  
M6

Extension for tube brushes with M6 threaded nipple  
Thread M6

577993 M6