

LESSMANN®
THE GERMAN BRUSH COMPANY**Tube brush Waved brass wire 0.15 mm, Brush Ø: 20mm****Order data**

Order number	577985 20
GTIN	4017359012826
Item class	57L

Description**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles. Bristles of waved wire, overall length 115 mm. Bristle length 80 mm long with crimped-on M6 threaded nipple.

Application:

For cleaning pipes, gratings, sleeves, heat exchangers, and cylinders. For use in machines (only clockwise rotation), use thread adapter No. 577990.

Technical description

Brush Ø D ₁	20 mm
Brush material	Brass wire
Adapter	Threaded nipple
Bristle thickness	0.15 mm
Type of product	Tube brush

Accessories

Extension for tube brushes with M6 threaded nipple Thread M6	577993 M6
Plastic handle for tube brushes with M6 threaded nipple Thread M6	577995 M6

M6 thread adapter, internal thread Shank Ø 6 mm Thread
M6

577990 M6