

LESSMANN®
THE GERMAN BRUSH COMPANY

Tube brush Waved brass wire 0.15 mm, Brush Ø: 10mm



Order data

Order number	577985 10
GTIN	4017359004456
Item class	57L

Description

Version:

Internal brushes with galvanised twisted wire core and plain helix of bristles. Bristles of waved wire, overall length 115 mm. Bristle length 80 mm long with crimped-on M6 threaded nipple.

Application:

For cleaning pipes, gratings, sleeves, heat exchangers, and cylinders. For use in machines (only clockwise rotation), use thread adapter No. 577990.

Technical description

Brush Ø D ₁	10 mm
Brush material	Brass wire
Adapter	Threaded nipple
Bristle thickness	0.15 mm
Type of product	Tube brush

Accessories

Plastic handle for tube brushes with M6 threaded nipple Thread M6	577995 M6
M6 thread adapter, internal thread Shank Ø 6 mm Thread M6	577990 M6

Extension for tube brushes with M6 threaded nipple
Thread M6

577993 M6