

LESSMANN®
THE GERMAN BRUSH COMPANY
Tube brush Waved steel wire 0.15 mm, Brush Ø: 20mm

Order data

| | |
|--------------|---------------|
| Order number | 577980 20 |
| GTIN | 4017359012932 |
| Item class | 57L |

Description
Version:

Internal brushes with galvanised twisted wire core and plain helix of bristles. Bristles of waved wire, overall length 115 mm. Bristle length 80 mm long with crimped-on M6 threaded nipple.

Application:

For cleaning pipes, gratings, sleeves, heat exchangers, and cylinders. For use in machines (only clockwise rotation), use thread adapter No. 577990.

Technical description

| | |
|------------------------|-----------------|
| Brush Ø D ₁ | 20 mm |
| Overall length L | 115 mm |
| Brush material | Steel wire |
| Adapter | Threaded nipple |
| Bristle thickness | 0.15 mm |
| Type of product | Tube brush |

Accessories

| | |
|---|-----------|
| Extension for tube brushes with M6 threaded nipple Thread M6 | 577993 M6 |
| | 577995 M6 |

Plastic handle for tube brushes with M6 threaded nipple
Thread M6

M6 thread adapter, internal thread Shank Ø 6 mm Thread
M6

577990 M6