

**Platform trolley, Type: 1200****Order data**

Order number	919811 1200
GTIN	4017976012001
Item class	96F

Description**Version:**

Welded steel sections and tubes, platform made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Wheel Ø	125 mm
Weight	14 kg
Platform area height	206 mm
Material of wheel	TPE
Safe working load	250 kg

Type	1200
Height	910 mm
Width	1100 mm
Platform area depth	450 mm
Platform area width	850 mm
Depth	450 mm
Type of product	Platform trolley