

**Cup brush X-LOCK, steel wire 0.30 mm, Brush Ø: 60X-LOCKmm****Order data**

Order number	573010 60X-LOCK
GTIN	4007220119150
Item class	55V

**Description****Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines. With **X-LOCK** quick-release clamping system for quick changing of brushes, no tools required.

**Application:**

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

**Technical description**

Brush Ø D <sub>1</sub>	65 mm
Length of brush section H <sub>1</sub>	20 mm
maximum speed	12500 min <sup>-1</sup>
Bristle thickness	0.3 mm
Series	X-LOCK
Brush material	Steel wire
Type of product	Cup brush

