

**Cup brush X-LOCK, stainless steel wire 0.30 mm, Brush Ø: 60X-LOCKmm****Order data**

Order number	573210 60X-LOCK
GTIN	4007220119198
Item class	55V

Description**Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines. With **X-LOCK** quick-release clamping system for quick changing of brushes, no tools required.

Application:

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

Technical description

Brush Ø D ₁	65 mm
Bristle thickness	0.3 mm
Length of brush section H ₁	20 mm
maximum speed	12500 min ⁻¹
Series	X-LOCK
Brush material	Stainless steel wire
Twisted knotting	waved
Type of product	Cup brush

