




Wheel brush X-LOCK, stainless steel wire 0.50 mm, Brush $\varnothing D_1 \times$ bore $\varnothing d_1$ / thread M: 125X-LOCKmm



Order data

Order number	571251 125X-LOCK
GTIN	4007220118771
Item class	55V

Description

Version:

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **X-LOCK** quick-release clamping system for quick changing of brushes, no tools required.

Technical description

Number of twisted knots	24
Brush $\varnothing D_1$	125 mm
maximum speed	12500 min ⁻¹
Bristle thickness	0.5 mm
Length of brush section H ₁	28 mm

Bristle width L ₁	12 mm
Series	X-LOCK
Brush material	Stainless steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush