

**Table trolley with 2 platforms up to 1200 kg, Type: 12497****Order data**

Order number	919865 12497
GTIN	4017976112497
Item class	96F

Description**Version:**

Welded steel and sections and tubes, platforms made of non-slip platform of marine plywood. 2 fixed wheels and 2 castors (with parking brake), high-grade resilient solid blue-grey rubber treadless tyres (200×50 mm), and hubs with roller bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

maximum load capacity	1200 kg
Width	910 mm
Weight	54 kg
Height of bottom shelf	283 mm

Height of top shelf	925 mm
Platform area depth	700 mm
Depth	700 mm
Load capacity of top shelf	500 kg
Height	925 mm
Wheel Ø	200 mm
Platform area width	700 mm
Type	12497
Type of product	Table trolleys