


Garant**Abrasive flap wheel roller, fabric (CER), Ø 100 × 100 mm, Grit: 80****Order data**

Order number	568463 80
GTIN	4062406287085
Item class	51M

Description**Version:**

Flap strips of abrasive cloth around the shank of the flap brush. Standard size **Ø 100×100 mm** or narrow version **Ø 100×50 mm** for grinding smaller areas. Mounting bore **Ø 19 mm** with multiple splines.

Application:

Ceramic grit (CER) ideal for working on stainless steels and nickel alloys. High removal rate and cool cut.

Note:

For matching the width of narrow rollers **Ø 100×50 mm** use the spacer ring pack No. 568439.

Technical description

Grinding media backing	Fabric
recommended speed	3700 min ⁻¹
Grit	80
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %

Roller Ø	100 mm
Roller width	100 mm
Product name attribute	Ø 100 × 100 mm
Bore Ø	19 mm
Type of product	Flap wheel roller fabric, slit

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
dry	suitable		