

Garant

Abrasive flap wheel roller, fleece (ZA), Ø 100 × 100 mm, Grit equivalent: 280



Order data

Order number	568477 280
GTIN	4062406288310
Item class	51M

Description

Version:

Standard size Ø 100×100 mm or narrow version Ø 100×50 mm for grinding smaller areas.
Mounting bore Ø 19 mm with multiple splines.

Especially wear-resistant and fine-structured fleece with Zirconium Aluminium Oxide (ZA). Ideal for use on stainless steel.

Application:

Fine fleece **for light cleaning work and a uniform surface finish.**

Note:

For matching the width of narrow rollers Ø 100×50 mm use the spacer ring pack No. 568439.

Technical description

Grinding media backing	Cleaning non-woven abrasive mesh
Grit equivalent	280
recommended speed	2800 min ⁻¹
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %

Roller Ø	100 mm
Roller width	100 mm
Product name attribute	Ø 100 × 100 mm
Bore Ø	19 mm
Type of product	Abrasive flap wheel roller, fleece

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		