



Digital caliper TESA-CAL IP67, Measuring range: 200mm



Order data

Order number	412760 200
GTIN	7630041148657
Item class	45A

Description

Version:

Large high-contrast display with 11 mm character height. More than 12000 hours service life, automatic standby after 10 minutes and automatic shutdown after 2 hours. ABS measuring mode. All-round protection against liquids. With thumb roller.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

External, internal, step and depth measurements.

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Measured value saving	Once-off setting of the zero position
Reversible reading	mm / inch
Calibration	A1
Measuring range	0 - 200 mm
Drive roller	yes
Number of batteries contained	1
Scale divisions	0.01 mm
Jaw length	50 mm

Auto switch-off	yes
Automatic stand-by circuit.	yes
Standard	ISO 13385
Depth gauge available	yes
Depth gauge	rectangular 3.7×1.3
Article no of the battery / rechargeable battery fitted	081560 CR2032
Working time	12000 hours
Scale divisions	0.0005 in
Measurement value and zero point preserved after reactivation from standby	yes
Digit height LCD display	11 mm
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------