

**Mini LED floodlight, Type: 7-SOUND****Order data**

Order number	081452 7-SOUND
GTIN	5708997359006
Item class	08C

Description**Version:**

Compact and powerful cordless LED floodlight for mobile use. The compact dimensions mean it is perfectly suitable for use as a hand lamp. The adjustable magnetic base allows the lamp to be used as a stationary light source.

With integral speaker, ideal for the workplace and building site. With remote control.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

IP Index of Protection: IP 65

ATEX zone: no

Illumination: 300 lm

Illumination step 2: 600 lm

Working life: 3 h

Lighting life stage 2: 6 h

Number of rechargeable batteries contained: 1

Technical description

Lighting life stage 2	6 h
-----------------------	-----

Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Illumination step 2	600 lm
Overall width	74 mm
Overall length	92 mm
Illumination	300 lm
Battery voltage	3.7 V
Weight	430 g
Working life	3 h
Power supply	Rechargeable battery-powered
Overall height	86 mm
Bulb	LED module
Battery capacity	5.2 A·h
IP Index of Protection	IP 65
ATEX zone	no
Manufacturer's designation	SOUNDLED S
Type of product	Floodlight