



Digital caliper TESA-CAL IP67 with rod type depth gauge, Measuring range: 150mm



Order data

Order number	412759 150
GTIN	7630041148640
Item class	45A

Description

Version:

Large high-contrast display with 11 mm character height. More than 12000 hours service life, automatic standby after 10 minutes and automatic shutdown after 2 hours. ABS measuring mode. All-round protection against liquids.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

External, internal, step and depth measurements.

Supplied with:

1 battery No. 081560 size CR2032.

Packaging: sturdy box

Standard: ISO 13385

Reversible reading: mm / inch

Depth gauge: Ø 1.6

IP Index of Protection: IP 67

Measured value saving: Once-off setting of the zero position

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Measurement deviation E MPE: ± 0.03 mm

Jaw length: 40 mm

Technical description

Working time	12000 hours
Measured value saving	Once-off setting of the zero position
Calibration	A1
Scale divisions	0.01 mm
Auto switch-off	yes
Measurement value and zero point preserved after reactivation from standby	yes
Standard	ISO 13385
Jaw length	40 mm
Measuring range	0 - 150 mm
Digit height LCD display	11 mm
Scale divisions	0.0005 in
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Reversible reading	mm / inch
Automatic stand-by circuit.	yes
Depth gauge	Ø 1.6
Depth gauge available	yes
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

Labelling laser-etched Type	018940
	011030 200

Calibration Calipers / depth gauges maximum measuring range 200 mm	
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------