



Telescopic single ladder, Number of steps: 10



Order data

Order number	966095 10
GTIN	
Item class	96Y

Description

Version:

Telescopic ladder of aluminium with stable triangular hollow section stiles, abrasion-resistant anodised. High-strength rung / stile connection. Deep square rungs with lined profiles to minimise the risk of slipping. Rung spacing 300 mm. Maximum load capacity 150 kg. Can be adjusted to different heights. When closed up, the ladder fits in a car boot.

Standard:**DIN EN 131.**

Ladders and platforms load capacity: 150 kg

Ladder length extended: 3 m

Ladder length closed: 0.79 m

Working height approx.: 3.8 m

Weight: 10.5 kg

Technical description

Ladder length extended	3 m
Standard	DIN EN 131
Weight	10.5 kg

Working height approx.	3.8 m
Ladder length closed	0.79 m
Ladders and platforms load capacity	150 kg
Type of product	Lean-to ladder