



Folding platform, standard version, Platform height: 2550mm



Order data

Order number	966311 2550
GTIN	4003866535132
Item class	96Z

Description

Version:

Folding platform with simple one-hand operation of the folding frame, with sturdy locking knob: Just one click to secure and release. Patented toe board unit. Easy-running attachment guide of hard plastic: The extension frames do not tilt when moved together. Scaffolding width: 0.72 m; scaffolding length: 1.8 m including castors with parking brakes \varnothing 125 mm. Can be extended to max. 7.65 m working height.

Standard:

EN 1004 (Gerüstklasse 3, belastbar bis 200 kg/m²).

Technical description

Working height approx.	4.55 m
Scaffolding height	3.65 m
Weight	78 kg
Ladders and platforms load capacity	200 kg
Type of product	Scaffolding

