

**Folding platform, standard version, Platform height: 1550mm****Order data**

Order number	966311 1550
GTIN	4003866535125
Item class	96Z

**Description****Version:**

Folding platform with simple one-hand operation of the folding frame, with sturdy locking knob: Just one click to secure and release. Patented toe board unit. Easy-running attachment guide of hard plastic: The extension frames do not tilt when moved together. Scaffolding width: 0.72 m; scaffolding length: 1.8 m including castors with parking brakes  $\varnothing$  125 mm. Can be extended to max. 7.65 m working height.

**Standard:**

EN 1004 (Gerüstklasse 3, belastbar bis 200 kg/m<sup>2</sup>).

**Technical description**

Scaffolding height	2.65 m
Working height approx.	3.55 m
Weight	68 kg
Ladders and platforms load capacity	200 kg
Type of product	Scaffolding

