

Garant **GRIDLINE****XL ToolCar roller cabinet, 20×20G, Number of drawers: 8****Order data**

Order number	914590 8
GTIN	4062406294861
Item class	9GT

**Description****Version:**

The ToolCar roller cabinet with depth 600 mm, with scratch resistant, anti-slip and extremely surface-friendly **GARANT GridLine mat**. Easy exchange of tray with other worktops (for example, bamboo). Valuables cupboard / side cupboard can be locked centrally together with drawers.

Cabinet stiles are clad with LDPE bumpers. In the event of collisions they reduce the damage to vulnerable surfaces and tools. Each with 2 ball-bearing fixed wheels and 2 castors, Ø 200 mm, with treadless TPU tyres, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

**Fitted with:**

Drawer front height, mm: 75; 75; 75; 75; 75; 125; 125; 125

**Supplied with:**

Supplied with dividers:

each 75 mm drawer 1 slotted partition No. 951520 size 75,

each 125 mm drawer 1 slotted partition No. 951520 size 125.

**Colour:**

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

**Note:**

For drawers of height 200 mm, more suitable components now include slotted dividers No. 951520 size 200, edge partitions No. 951570 size 200, and divider inserts No. 951741 – 951821 each in size 200.

See group 95 for further accessories and dividing material. Suitable dividing material:

Slotted edge partitions No. 951570 size 75 and size 125;

Slotted dividers No. 951520 size 75 and size 125;

Divider inserts No. 951721 – 951821 size 75 and No. 951731 – 951821 size 125.

## Technical description

Series	ToolCar
Drawer usable width in G	20
Drawer usable depth in G	20
Drawer usable width	500 mm
Individual drawer release system	One-hand
Weight	125.5 kg
total maximum load capacity	600 kg
Width	820 mm
Depth	630 mm
Number of drawers	8
Drawer usable depth	500 mm
Height	1080 mm
Drawer usable area in G	20×20
Drawer/pull-out shelf load capacity	50 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Drawer usable width × usable depth in G	20×20G
Cylinder lock	modular barrel
Type of product	Roller cabinet

**Accessories**

Slotted dividersDepth 20G suitable for drawer front height  
125 mm

951520 125

Slotted dividersDepth 20G suitable for drawer front height  
75 mm

951520 75