

Garant**Pair of gloves MASTER FIT, Glove size: 6****Order data**

Order number	094303 6
GTIN	4062406295417
Item class	01H

Description**Version:**

MASTER FIT fitter's gloves. With innovative water-based PU nitrile coating for the utmost demands regarding precision, flexibility and touch sensitivity in dry working environments. Finely structured surface on the palm of the hand due to complex finishing process. Suitable for touch screens, allowing smartphone and other touch screens to be operated without removing the gloves. Long life through very high abrasion resistance. DMF-free and Öko-Tex certified. MASTER FIT fitter's gloves with raised dots on the palm.

Standard:

EN 388, EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	6
Type of glove	Multi-purpose gloves
Series	MASTER FIT

Protection category	Category II
Clothing standard	Oeko-Tex Standard 100
Contents	12
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	Suitable for touch screens
Glove characteristics	DMF-free
EN 388	4131X
Backing material	Lycra® / polyamide
Coating	water-based PU/nitrile
Coating variant	The palms of the hands
Application range	All-round
Application range	Precision
Length	255 mm
Colour	blue / black
Knitted technology	15G
AQL	G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor.
Application	reusable
Type of product	Multi-purpose gloves