

Garant**Mesh trolley TG9 with 5 loading platforms, Type: TG98****Order data**

Order number	918565 TG98
GTIN	4062406295646
Item class	9GT

Description**Version:**

Welded steel construction, shelves of **chipboard** with anthracite-coloured scratch-resistant surface. Adjustable at 40 mm intervals. Fold-away handle at the side with 2-component Haptoprene coating permits a very wide door opening angle. With 2 ball-bearing fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres, Ø 200 mm. Can be centrally locked by 2-component Haptoprene push handle using a cylinder lock.

Standard:

EN 1757-3

Optional extras:

Additional shelf No. 918578.

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Load capacity of each loose shelf	95 kg
-----------------------------------	-------

Total load capacity	500 kg
Depth	810 mm
Height	1835 mm
Platform area width	1200 mm
Platform area depth	800 mm
Weight	179 kg
Width	1400 mm
Wheel Ø	200 mm
Door opening angle	250 degrees
Height adjustment interval	40
Cylinder lock	modular barrel
Type of product	Enclosed trolley

Accessories

Intermediate shelf for slotting into mesh trolley TG9
Platform area depth 800 mm

918578 800