

Garant**Safety coupling Hose connection, Hose connection internal Ø (nominal bore): 11mm****Order data**

Order number	080272 11
GTIN	4062406296964
Item class	01A

Description**Version:**

The GARANT safety shut-off is a high-performance coupling of galvanised steel, with extremely high flow rate capacity. New improved single-handed operation.

Rate of flow: 2250 ltr/min, maximum operating pressure 16 bar. Satisfies the ISO standard 4414 and EN 983.

Note:

See No. 080290 – 080293 for suitable coupling adapters.

The GARANT series satisfies Euro standard 7.6 (nominal Ø 7.6 mm, Euro profile) and is compatible with all popular systems.

Technical description

maximum operating pressure	16 bar
Flow rate	2250 l/min
Hose connection internal Ø (nominal bore)	11 mm
Type of product	Coupling

Accessories

Coupling adaptor with hose coupling5-piece set Hose
connection internal \varnothing (nominal bore) 11 mm

080292 11

Coupling adaptor with Stream-Line Hose connection
internal \varnothing (nominal bore) 11 mm

080293 11