


**Garant****Velour-backed abrasive disc (A) 15 holes, Ø 150 mm, Grit: 80****Order data**

Order number	567553 80
GTIN	4062406296995
Item class	51M

**Description****Version:**

Velour-backed abrasive disc with **paper backing**. Dust-repellent coating prevents premature clogging. The back is covered with velour loops.

Velour-backed abrasive disc with open distribution, aluminium oxide (A). Ideally suited to materials that have a high tendency to clogging.

**Application:**

On **orbital sanders** with hook and loop pads e.g.No. 567990 (dust extraction available).

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

**Technical description**

Grit	80
Disc Ø	150 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 150 mm
Number of dust extraction holes	15
Propulsive equipment	Orbital sander
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		