

3M**Mini-linishing belt Ø 90×100 mm, 947A, Grit: 60****Order data**

Order number	568531 60
GTIN	8718734418504
Item class	53M

Description**Version:**

Mini linishing belts Ø 90×100 mm (289×100 mm).

Premium linishing belt with precisely formed **Cubitron™ II** ceramic grit (self-sharpening). With grinding aids for even cooler grinding.

Application:

For use on surface grinding and burnishing machines with backing rollers No. 568570 – 568577 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

Clear step forward in performance on **materials that are difficult to machine** such as stainless steel, nickel alloys, chrome alloys and aluminium.

Technical description

Linishing belt width	100 mm
Linishing belt length	289 mm
Grit	60
Linishing belt Ø	90 mm
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %

Manufacturer's designation	947A
Type of product	Finishing belt

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable only under restricted conditions		
dry	suitable		