


3M**Mini-linishing belt Ø 90×100 mm, 337DC, Grit: 120****Order data**

Order number	568534 120
GTIN	8718734418580
Item class	53M

Description**Version:**

Mini linishing belts Ø 90×100 mm (289×100 mm).

Defined blocks pressed in as abrasive grit. High grit density for very long working life. **No clogging** due to defined channels. **Consistent surface quality** over the entire grinding process, even on thin sheets.

Application:

For use on surface grinding and burnishing machines with backing rollers No. 568570 – 568577 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

Technical description

Linishing belt Ø	90 mm
Linishing belt length	289 mm
3M grit designation	A160
Grit	120
Linishing belt width	100 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

Manufacturer's designation	337DC
Type of product	Finishing belt

User data

	Suitability	V_c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
dry	suitable		