

3M**Mini-linishing belt Ø 90×100 mm, 237AA, Grit: 120****Order data**

| | |
|--------------|---------------|
| Order number | 568537 120 |
| GTIN | 8718734418634 |
| Item class | 53M |

Description**Version:**

Mini linishing belts Ø **90×100 mm** (289×100 mm).

The fine-structured pyramidal surface guarantees the **best finish and very long working life**. Particularly suitable for the intermediate grinding of stainless steel sheets.

Application:

For use on surface grinding and burnishing machines with backing rollers No. 568570 – 568577 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

Technical description

| | |
|---|---------|
| 3M grit designation | A160 |
| Linishing belt Ø | 90 mm |
| Linishing belt width | 100 mm |
| Linishing belt length | 289 mm |
| Grit | 120 |
| Grinding medium code | A |
| Iron, sulphur and chlorine constituents | < 0.1 % |

| | |
|----------------------------|----------------|
| Manufacturer's designation | 237AA |
| Type of product | Finishing belt |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|----------------------|-----------------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| CuZn | suitable only under restricted conditions | | |
| Paint | suitable | | |
| dry | suitable | | |