

**3M****Mini-linishing belt Ø 100×100 mm, 237AA, Grit: 240****Order data**

Order number	568538 240
GTIN	8718734418702
Item class	53M

**Description****Version:**

Mini linishing belts Ø **100×100 mm** (314×100 mm).

The fine-structured pyramidal surface guarantees the **best finish and very long working life**. Particularly suitable for the intermediate grinding of stainless steel sheets.

**Application:**

For use on surface grinding and burnishing machines with backing rollers No. 568570 – 568577 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

**Technical description**

Grit	240
Linishing belt width	100 mm
Linishing belt length	320 mm
Linishing belt Ø	100 mm
3M grit designation	A080
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

Manufacturer's designation	237AA
Type of product	Finishing belt

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
CuZn	suitable only under restricted conditions		
Paint	suitable		
dry	suitable		