

Garant**Mini-linishing belt Ø 100×100 mm, Grit equivalent: 180****Order data**

Order number	568558 180
GTIN	4062406297947
Item class	51M

Description**Version:**

Mini linishing belts Ø **100×100 mm** (314×100 mm).

Fleece mini-linishing belts for blending in, matting and finishing.

With film backing, for light-duty use on all backing rollers.

Application:

For use on surface grinding and burnishing machines with backing rollers No. 568570 – 568577 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

Technical description

Grit equivalent	180
Colour	red
Linishing belt width	100 mm
Linishing belt Ø	100 mm
Version	A medium
Linishing belt length	320 mm
Iron, sulphur and chlorine constituents	< 0.1 %

Type of product

Linishing belt

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		

Accessories

Backing roller Ø 90×100 mm Type AIR

568575 AIR