


Garant**Backing roller Ø 100×100 mm, Type: AIR****Order data**

Order number	568577 AIR
GTIN	4062406297961
Item class	56S

Description**Version:**

Mounting bore Ø 19 mm with double keyway.

Pneumatic version, the degree of hardness can be set individually. Adapter for bike pumps included.

Application:

To take mini-finishing belts No. 568531 – 568561.

Technical description

Degree of hardness	AIR
Colour	black
Type	pneumatic
Roller Ø	100 mm
Roller width	100 mm
Bore Ø	19 mm
Type of product	Burnishing roller carrier

