

## PRYOR

**Numeral letter punch set, 27 pieces Normal script A – Z, &, Character height: 2mm**



### Order data

Order number	085430 2
GTIN	5022044001206
Item class	08W

### Description

#### Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

**High performance precision punches**, chemically nickel-plated, very long service life.

**Normal script**; i. e. the punched character can be read directly on the component.

#### Application:

For punching into materials with a **strength up to 1200 N/mm<sup>2</sup>**.

#### Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

#### Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

### Technical description

Shank thickness	6.35
Character height	2 mm

overall length	63.5 mm
Type of product	Hand punch

## Accessories

Letter punch – individual Normal script A – Z Character height / Characters 2/Q mm	085431 2/Q
Letter punch – individual Normal script A – Z Character height / Characters 2/Y mm	085431 2/Y
Letter punch – individual Normal script A – Z Character height / Characters 2/A mm	085431 2/A
Letter punch – individual Normal script A – Z Character height / Characters 2/N mm	085431 2/N
Letter punch – individual Normal script A – Z Character height / Characters 2/& mm	085431 2/&
Letter punch – individual Normal script A – Z Character height / Characters 2/X mm	085431 2/X
Letter punch – individual Normal script A – Z Character height / Characters 2/H mm	085431 2/H
Letter punch – individual Normal script A – Z Character height / Characters 2/I mm	085431 2/I
Letter punch – individual Normal script A – Z Character height / Characters 2/R mm	085431 2/R
Letter punch – individual Normal script A – Z Character height / Characters 2/K mm	085431 2/K
Letter punch – individual Normal script A – Z Character height / Characters 2/M mm	085431 2/M
Letter punch – individual Normal script A – Z Character height / Characters 2/S mm	085431 2/S
Letter punch – individual Normal script A – Z Character height / Characters 2/F mm	085431 2/F
Letter punch – individual Normal script A – Z Character height / Characters 2/U mm	085431 2/U

Letter punch – individualNormal script A – Z Character height / Characters 2/P mm	085431 2/P
Letter punch – individualNormal script A – Z Character height / Characters 2/T mm	085431 2/T
Letter punch – individualNormal script A – Z Character height / Characters 2/W mm	085431 2/W
Letter punch – individualNormal script A – Z Character height / Characters 2/L mm	085431 2/L
Letter punch – individualNormal script A – Z Character height / Characters 2/J mm	085431 2/J
Letter punch – individualNormal script A – Z Character height / Characters 2/D mm	085431 2/D
Letter punch – individualNormal script A – Z Character height / Characters 2/V mm	085431 2/V
Letter punch – individualNormal script A – Z Character height / Characters 2/G mm	085431 2/G
Letter punch – individualNormal script A – Z Character height / Characters 2/O mm	085431 2/O
Punch holder Type GRIP	085475 GRIP
Letter punch – individualNormal script A – Z Character height / Characters 2/C mm	085431 2/C
Letter punch – individualNormal script A – Z Character height / Characters 2/B mm	085431 2/B
Letter punch – individualNormal script A – Z Character height / Characters 2/Z mm	085431 2/Z
Letter punch – individualNormal script A – Z Character height / Characters 2/E mm	085431 2/E