



Diamond grinding compound 10 g, universally soluble Polycrystalline, Grit diamond grinding compound: 9µm



Order data

Order number	552350 9
GTIN	4027497101443
Item class	56L

Description

Version:

Silicone-free diamond paste in a handy spray can.

Synthetic poly-crystalline diamond in 10g spray for quick polishing results.

Application:

The bonding, which can be mixed **with alcohol or water in any proportion**, ensures an optimum lubrication film. Easy and environmentally friendly cleaning of tools and components with water. Leaves no residues.

Ideal for steels and titanium with hardness greater than 60 HRC. Very economical, since the polycrystalline structure of the diamond constantly reveals new cutting edges and the polishing proceeds.

Technical description

Colour code	red
Grit diamond grinding compound	9 µm
Grit designation	medium
Grinding media	Diamond
Grinding medium code	D
Type of product	Grinding compound

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	1-3 m/s	P
Steel < 55 HRC	suitable	1-3 m/s	H
Steel < 60 HRC	suitable	1-3 m/s	H
Steel < 67 HRC	suitable	1-3 m/s	H
Carbide (HM)	suitable	1-3 m/s	
INOX	suitable	1-3 m/s	
Ti	suitable	1-3 m/s	
Plastic, GRP	suitable	1-3 m/s	
Stone	suitable	1-3 m/s	
dry	suitable		