

Garant**Roll of abrasive fleece, 115 mm × 10 m, Fleece structure: 280****Order data**

| | |
|--------------|---------------|
| Order number | 556087 280 |
| GTIN | 4062406300883 |
| Item class | 51M |

Description**Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding. High-performance fleece with **extremely dense grit distribution** deep into the fibres of the material. The special type of fleece structure permits **aggressive grinding characteristics**, a very long working life without clogging and an even **more uniform finish**.

Advantage:

- **Adapts to the component shape.**
- **The open structure prevents clogging and reduces heat development.**
- **Even and reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

Application:

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Medium / medium fine:** Can be used universally for removing rust film, light soiling, discolouration; for rubbing down ground or brushed surfaces, or for degreasing and cleaning prior to painting.

Technical description

| | |
|---|-------------------------|
| Grit designation | medium fine |
| Colour | red |
| Version | A Very Fine |
| Fleece structure | 280 |
| Grit equivalent | 280 - 360 |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Roller width | 115 mm |
| Roll length | 10 m |
| Product name attribute | 115 mm × 10 m |
| Type of product | Roll of abrasive fleece |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Stone | suitable only under restricted conditions | | |
| Paint | suitable | | |
| Uni | suitable | | |

| | |
|-------------|---|
| wet maximum | suitable only under restricted conditions |
| dry | suitable |

Accessories

| | |
|------------|--------|
| Hand block | 556020 |
| Mandrel | 556030 |