

Garant GRIDLINE

Mobility unit for GridLine tool cabinets, factory fitted, suitable for casing depth in G: 24



Order data

Order number	958481 24
GTIN	4062406299873
Item class	9GK

Description

Version:

GridLine mobility unit consisting of 2 galvanized sheet metal cross beams. Completely assembled with set of wheels and 1 set of 2-component Haptoprene® push handle. For bolting on to GridLine cabinets and tool cabinets. **Push the cabinet from the side.**

Factory fitted when GridLine tool cabinets and mobility unit are ordered at the same time.

Suitable for:

Tool cabinets No. 930505 – 930735.

Supplied with:

1 × cross beam with 2 castors with parking brakes, 1 × cross beam with 2 fixed wheels, 1 × push handle set.

Attention:

Because of the risk of tipping over, when installing the mobility unit comply strictly with the specified maximum cabinet height.

When calculating the load capacity, please take account of the tare weight of the cabinet / tool cabinet.

Note:

Mobility unit suitable for GridLine tool cabinets up to a maximum height of 1000 mm. The maximum height for 24×24G tool cabinets is 900 mm. Maximum load capacity overall 600 kg.

Mandatory requirement that any drawers are fitted with one-hand individual drawer release.

Technical description

Carriage height	160 mm
Depth	600 mm
Castor Ø	125 mm
maximum load capacity	600 kg
Fixed wheel Ø	125 mm
Type of product	Wheels and push handle