

**Welder's boot, anthracite VX 7380 PERB, S3 NB, EU shoe size: 40****Order data**

Order number	092814 40
GTIN	4044348369838
Item class	09C

Description**Version:**

Welder's boots VX 7380 PERB for extreme conditions. Gutter system for draining hot liquids.

- **Closed tongue.**
- **Perbunan outer sole, anthracite.**
- **SECURA VARIO® heel cushioning.**
- **Real leather insole.**
- **ERGO-COOL® comfort mid-sole inlay.**

Standard:

EN ISO 20349-2:2017 SRC WG WRU FO HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Wide version XB, see No. 092815.

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered. Includes the damping element red and green

Technical description

Gender	Unisex
--------	--------

Standard	Inlay type-tested according to DGUV regulation 191
Puncture resistance	Steel
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
EU shoe size	40
Characteristics	Vario® damping
Material of protective toe-cap	Aluminium
Protection class	S3
Type of product	Safety boots