



Welder's boots, anthracite VX 7380 PERB, S3 XB, EU shoe size: 37



Order data

Order number

092815 37

GTIN

Item class

09C

Description

Version:

Foundryman's and welder's boots VX 7380 PERB for extreme conditions. Gutter system for draining hot liquids.

- **Closed tongue.**
- **Outer sole steel, anthracite.**
- **SECURA VARIO® heel cushioning.**
- **Real leather lining.**
- **Real leather insole.**
- **ERGO-COOL® comfort mid-sole inlay.**

Standard:

EN ISO 20349:2010 SRC WG WRU FO HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

Note re advertising text:

Safety shoes from Steitz Secura offer a multi-width system.

Protection class: S3

Material of protective toe-cap: Aluminium

Puncture resistance: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):
Over 200 °C

Standard: Indlægsforsyning typegodkendt iht. DGUV-regel 191
Characteristics: Vario® damping

Technical description

| | |
|--|---|
| Behaviour of outer sole in response to contact temperature (melting point of the outer sole) | Over 200 °C |
| EU shoe size | 37 |
| Gender | Unisex |
| Protection class | S3 |
| Puncture resistance | Steel |
| Characteristics | Vario® damping |
| Standard | Indlægsforsyning typegodkendt iht. DGUV-regel 191 |
| Material of protective toe-cap | Aluminium |
| Type of product | Safety boots |