

Garant
Thread cutting set with tap sets, 3 pieces, for metric threads: M3-12

Order data

Order number	145112 M3-12
GTIN	4062406299897
Item class	11K

Description
Version:

Strong sheet metal case with carrying handle and 2 offset catches. Each tool is securely stored in its own holder and immediately ready to hand. The taps are raised up vertically when the lid is opened. For more detailed descriptions of the content see individual products.

Content:

1 each tap set, 3 pieces, No. 130150: Size M3; M4; M5; M6; M8; M10; M12

1 each die No. 140300: Size M3; M4; M5; M6; M8; M10; M12

1 each jobber drill No. 114150: Size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2

1 each adjustable tap wrench No. 148410: Size 1; 2

1 tap wrench with ratchet No. 148700: Size 85

1 each die stock No. 149310: Size 20×5; 20×7; 25×9; 30×11; 38×14

1 thread gauge No. 477000: Size M/W

1 screwdriver No. 664300: Size 3×60

Flank angle: 60 °

Technical description

for metric threads	M3 – M12
Height	58 mm

Length	418 mm
Width	229 mm
Thread type	M
Flank angle	60 °
Type of product	Die

Accessories

HSS jobber drill N Ø DC h8 (mm or inch) 5	114150 5
HSS jobber drill N Ø DC h8 (mm or inch) 6,8	114150 6,8
Die 6g M M4	140300 M4
Die stock for die Ø × height 20X7 mm	149310 20X7
Hand tap set M M4	130150 M4
Hand tap set M M5	130150 M5
Die 6g M M10	140300 M10
Die stock for die Ø × height 30X11 mm	149310 30X11
HSS jobber drill N Ø DC h8 (mm or inch) 10,2	114150 10,2
Hand tap set M M6	130150 M6
Hand tap set M M8	130150 M8
Hand tap set M M10	130150 M10
3X60	664300 3X60
T-tap wrench with ratchet Overall length 85 mm	148700 85
Die 6g M M8	140300 M8
Die stock for die Ø × height 20X5 mm	149310 20X5
Die stock for die Ø × height 25X9 mm	149310 25X9
Die stock for die Ø × height 38X14 mm	149310 38X14
Thread gauge for threads M/W	477000 M/W
Die 6g M M5	140300 M5
Die 6g M M3	140300 M3

Hand tap set M M3	130150 M3
HSS jobber drill N Ø DC h8 (mm or inch) 3,3	114150 3,3
HSS jobber drill N Ø DC h8 (mm or inch) 4,2	114150 4,2
HSS jobber drill N Ø DC h8 (mm or inch) 2,5	114150 2,5
Die 6g M M12	140300 M12
Die 6g M M6	140300 M6
HSS jobber drill N Ø DC h8 (mm or inch) 8,5	114150 8,5
Tap wrench, adjustable Type 2	148410 2
Tap wrench, adjustable Type 1	148410 1
Sheet metal case empty for thread cutting set for metric threads M3-12	145605 M3-12
Hand tap set M M12	130150 M12