



Thread cutting set with tap sets, 3 pieces, for metric threads: M3-20



Order data

| | |
|--------------|---------------|
| Order number | 145117 M3-20 |
| GTIN | 4062406301521 |
| Item class | 12K |

Description

Version:

Strong sheet metal case with carrying handle and 2 offset catches. Each tool is securely stored in its own holder and immediately ready to hand. The taps are raised up vertically when the lid is opened. For more detailed descriptions of the content see individual products.

Content:

- 1 each tap set, 3 pieces, No. 130250: Size M3; M4; M5; M6; M8; M10; M12; M14; M16; M18; M20
- 1 each die No. 140330: Size M3; M4; M5; M6; M8; M10; M12; M14; M16; M18; M20
- 1 each adjustable tap wrench No. 148410: Size 1.1/2; 3
- 1 each die stock No. 149310: Size 20×5; 20×7; 25×9; 30×11; 38×14; 45×18
- 1 thread gauge No. 477000: Size M/W
- 1 screwdriver No. 664300: Size 3×60
- 1 tap wrench with ratchet No. 148700: Size 85; 110

Technical description

| | |
|--------------------|----------|
| for metric threads | M3 - M20 |
| Height | 63 mm |
| Length | 532 mm |
| Width | 256 mm |

| | |
|-----------------|------------|
| Thread type | M |
| Flank angle | 60 degrees |
| Type of product | Die |

Accessories

| | |
|---------------------------------------|--------------|
| Die6g M M14 | 140330 M14 |
| Hand tap set M M6 | 130200 M6 |
| Die stock for die Ø × height 25X9 mm | 149310 25X9 |
| Hand tap set M M5 | 130200 M5 |
| Hand tap set M M18 | 130200 M18 |
| Tap wrench, adjustable Type 1.1/2 | 148410 1.1/2 |
| Die6g M M3 | 140330 M3 |
| Die6g M M12 | 140330 M12 |
| Hand tap set M M10 | 130200 M10 |
| Hand tap set M M14 | 130200 M14 |
| Die stock for die Ø × height 20X7 mm | 149310 20X7 |
| Hand tap set M M16 | 130200 M16 |
| Die6g M M18 | 140330 M18 |
| Die stock for die Ø × height 30X11 mm | 149310 30X11 |
| Hand tap set M M20 | 130200 M20 |
| Die6g M M6 | 140330 M6 |
| Die6g M M4 | 140330 M4 |
| Hand tap set M M8 | 130200 M8 |
| Hand tap set M M12 | 130200 M12 |
| Die stock for die Ø × height 38X14 mm | 149310 38X14 |
| Thread gauge for threads M/W | 477000 M/W |
| Hand tap set M M3 | 130200 M3 |
| Die stock for die Ø × height 20X5 mm | 149310 20X5 |

| | |
|------------------------------------------------------------------------|--------------|
| Die6g M M20 | 140330 M20 |
| T-tap wrench with ratchet Overall length 110 mm | 148700 110 |
| Die6g M M16 | 140330 M16 |
| Die stock for die Ø × height 45X18 mm | 149310 45X18 |
| Die6g M M5 | 140330 M5 |
| T-tap wrench with ratchet Overall length 85 mm | 148700 85 |
| Die6g M M8 | 140330 M8 |
| Tap wrench, adjustable Type 3 | 148410 3 |
| Die6g M M10 | 140330 M10 |
| Sheet metal case empty for thread cutting set for metric threads M3-20 | 145610 M3-20 |