



Thread cutting set with tap sets, 3 pieces, for metric threads: M3-12



Order data

Order number	145117 M3-12
GTIN	4062406301514
Item class	12K

Description

Version:

Strong sheet metal case with carrying handle and 2 offset catches. Each tool is securely stored in its own holder and immediately ready to hand. The taps are raised up vertically when the lid is opened. For more detailed descriptions of the content see individual products.

Content:

- 1 each tap set, 3 pieces, No. 130250: Size M3; M4; M5; M6; M8; M10; M12
- 1 each die No. 140330: Size M3; M4; M5; M6; M8; M10; M12
- 1 each jobber drill No. 114030: Size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2
- 1 each adjustable tap wrench No. 148410: Size 1; 2
- 1 tap wrench with ratchet No. 148700: Size 85
- 1 each die stock No. 149310: Size 20×5; 20×7; 25×9; 30×11; 38×14
- 1 thread gauge No. 477000: Size M/W
- 1 screwdriver No. 664300: Size 3×60

Technical description

for metric threads	M3 – M12
Height	55 mm

Length	416 mm
Width	221 mm
Thread type	M
Flank angle	60 degrees
Type of product	Die

Accessories

Die6g M M8	140330 M8
Hand tap set M M5	130200 M5
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 8	114030 8
Die stock for die Ø × height 30X11 mm	149310 30X11
Die6g M M4	140330 M4
Tap wrench, adjustable Type 2	148410 2
Die stock for die Ø × height 20X7 mm	149310 20X7
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 3,3	114030 3,3
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 5	114030 5
Hand tap set M M6	130200 M6
Die6g M M10	140330 M10
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 10,2	114030 10,2
Die6g M M12	140330 M12
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 8,5	114030 8,5
Die6g M M5	140330 M5
Hand tap set M M12	130150 M12
Die6g M M6	140330 M6

Thread gauge for threads M/W	477000 M/W
Hand tap set M M8	130200 M8
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 2,5	114030 2,5
Die stock for die Ø × height 38X14 mm	149310 38X14
T-tap wrench with ratchet Overall length 85 mm	148700 85
Hand tap set M M10	130200 M10
Die stock for die Ø × height 25X9 mm	149310 25X9
Die stock for die Ø × height 20X5 mm	149310 20X5
Hand tap set M M3	130200 M3
Hand tap set M M12	130200 M12
Die6g M M3	140330 M3
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 4,2	114030 4,2
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 6	114030 6
Tap wrench, adjustable Type 1	148410 1
HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 6,8	114030 6,8
Sheet metal case empty for thread cutting set for metric threads M3-12	145610 M3-12