



## RackGuard™ racking leg protector narrow, Type: LLR



### Order data

Order number	994420 LLR
GTIN	5056116705990
Item class	99T

### Description

#### Version:

The RackGuard™ racking leg protector protects the exposed racking legs from lateral and frontal impacts by industrial trucks, causing scratches and damage. The impact energy is directed around the foot instead of through it, thereby reducing damage and protecting the stability of the racking system. Rubber inlays ensure safe retention on commonly-used racking legs. Honeycomb structure for attenuation of impacts. Maximum impact energy at 90°: 1000 Joules. Impact zone 0 – 600 mm. Deformation at maximum energy: 20 mm. Very good resistance to weather, very good colour fastness.

#### Standard:

EN 15 512, FEM 10.2.02, AS 4084

#### Suitable for:

Schulte pallet racking frame profile S610-M18-U. Stand width 76 mm. Pallet racks No. 991202 all sizes; No. 991207 all sizes; No. 991212 sizes 2500, 3000, 3500; No. 991217 sizes 2500, 3000, 3500. Pallet racks from SSI Schäfer with pedestal profile P73.

#### Note:

Racking leg protector for other racks can be offered on request.

### Technical description

Height	600 mm
Depth B max.	80 mm
Width A max.	85 mm
Weight	1.9 kg
Manufacturer's designation	RackGuard (S) LLR
Type of product	Crash barrier