



## Cordless work lamp, Type: IF3R



### Order data

Order number	081271 IF3R
GTIN	4058205020237
Item class	04B

### Description

#### Version:

Small, well-designed and high-power: the iF3R is a floodlight with huge light output. The floodlight is only 14 cm long, but delivers up to 1000 Lumen to the location and can be adjusted to five brightness settings. At the lowest setting the iF3R delivers a full 15 hours of illumination. It is charged using the Magnetic Charge System, consequently even without its cover the connections are watertight (IP54). Base, magnet and hook ensure flexible positioning. Thanks to the Cooling

Technology the COB-LED is protected against overheating.

- **Small floodlight with a surprisingly high light output.**
- **Flexible application and alignment thanks to the adjustable base, magnet and hook.**
- **Easy charging by the Magnetic Charge System.**
- **Cooling Technology for continuous operation without overheating.**
- **Five dimming settings.**

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

ATEX zone: no

Illumination: 100 - 1000 lm

Working life: 1.5 - 15 h

CRI value: 80

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

## Technical description

Power supply	Rechargeable battery-powered
Number of rechargeable batteries contained	1
Colour temperature	5400 - 6600 K
Type of rechargeable battery	Lithium-ion
ATEX zone	no
Weight	392 g
IP Index of Protection	IP 54
Bulb	LED module
Working life	1.5 - 15 h
Battery capacity	4 A·h
Overall length	140 mm
Illumination	100 - 1000 lm
Overall width	36 mm
Battery voltage	3.7 V
Overall height	71 mm
CRI value	80
Manufacturer's designation	iF3R
Type of product	Work lamp