



Cordless floodlight, Type: IF4R



Order data

Order number	081272 IF4R
GTIN	4058205016209
Item class	04B

Description

Version:

Fix, secure, set up – the compact iF4R is easy to transport and need not be held when you need both hands free. The rechargeable floodlight with its five brightness setting thus lends itself to your application:

with its magnet, flexible base and handle you always have light where you need it. Thanks to the integral powerbank, the iF4R not only gives you up to 15 hours of illumination, it also provides new energy for your mobile phone.

- **Especially compact.**
- **Integral magnet for easy attachment to metal surfaces (such as to steel girders).**
- **Five brightness settings with up to 2,500 Lumen.**
- **The integral powerbank supplies power to mobile phones and other mobile devices.**
- **Efficient heat sink for a long working life and optimum performance**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

ATEX zone: no

Illumination: 200 - 2500 lm

Working life: 1.3 - 15 h

CRI value: 80

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Technical description

Colour temperature	5400 - 6600 K
ATEX zone	no
Working life	1.3 - 15 h
Overall length	235 mm
CRI value	80
Battery voltage	3.7 V
Illumination	200 - 2500 lm
Power supply	Rechargeable battery-powered
Bulb	LED module
Weight	1060 g
IP Index of Protection	IP 54
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Battery capacity	8 A·h
Overall height	111 mm
Overall width	44 mm
Manufacturer's designation	iF4R
Type of product	Floodlight