



Cordless floodlight with Bluetooth speaker, Type: IF4R-MUSIC



Order data

Order number	081273 IF4R-MUSIC
GTIN	
Item class	04B

Description

Version:

Now you can have music in your day-to-day working life! The much loved iF4R floodlight has been given a very special upgrade: A high-quality speaker has been incorporated into the iF4R music. This can be connected via Bluetooth to the smart phone and thus operate as a jobsite radio. The iF4R music delivers 2500 Lumen light intensity, divided into five

brightness settings. The music floodlight is charged by the Magnetic Charge System.

- **An integral magnet allows easy attachment to metal surfaces (such as steel girders).**
- **Five brightness settings with up to 2500 Lumen light intensity, controlled by a multi-function switch.**
- **The integral speaker can be controlled by Bluetooth.**
- **Easy charging by the Magnetic Charge System.**
- **Large sturdy handle means it is easy to transport.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Overall width	47 mm
Overall height	110 mm

Weight	1139 g
Type of rechargeable battery	Lithium-ion
Colour temperature	5400 - 6600 K
Power supply	Rechargeable battery-powered
Bulb	LED module
Overall length	235 mm
ATEX zone	no
Illumination time	1.5 - 15 h
Illumination	200 - 2500 lm
Number of rechargeable batteries contained	1
IP Index of Protection	IP 54
CRI value	80
Battery capacity	8 Ah
Battery voltage	3.7 V
Manufacturer's designation	iF4R music
Interface	Bluetooth interface
Type of product	Floodlight