



Cordless work lamp, Type: IW3R



Order data

Order number	081457 IW3R
GTIN	4058205020176
Item class	04B

Description

Version:

Long working days are nothing unusual for the craftsman. So that the smart phone remains available as long as its owner, a powerbank ranks as essential equipment. The new iW3R is a sturdy and reliable powerbank with the additional feature of a spotlight which brings 320 Lumen of light into the darkness whenever it's needed. Thus the iW3R is a valuable additional resource for the craftsman, do-it-yourselfer, site worker, or indeed anyone looking for a reliable powerbank with an inbuilt torch.

- **Powerbank with 4000 mAh battery capacity.**
- **Lamp with spotlight and 320 Lumen lighting power.**
- **Battery status display.**
- **Two dimming settings.**
- **Closed connections with IP54 rating.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

ATEX zone: no

Illumination: 30 - 320 lm

Working life: 3.5 h

CRI value: 70

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Technical description

Illumination	30 - 320 lm
Power supply	Rechargeable battery-powered
Number of rechargeable batteries contained	1
Weight	143 g
Overall height	32 mm
ATEX zone	no
Battery voltage	3.7 V
CRI value	70
Overall length	122 mm
Overall width	32 mm
Bulb	LED module
IP Index of Protection	IP 54
Type of rechargeable battery	Lithium-ion
Working life	3.5 h
Battery capacity	4 A·h
Colour temperature	5400 - 6600 K
Manufacturer's designation	iW3R
Type of product	Work lamp