

**Cordless pen torch, Type: IW4R****Order data**

Order number	081458 IW4R
GTIN	4058205016261
Item class	04B

**Description****Version:**

Nothing is faster than light. And no lamp is quicker to hand than the iW4R – the rechargeable work light for the trousers pocket! Hardly any bigger than a ball-point pen, it provides the necessary illumination for every operation. The flexible mounting is versatile and can be attached using the integral magnet, and aligned to the desired angle. Thanks to the battery status display you always know how long your iW4R will remain ready to perform – but with up to four hours power it's not going to go dark very quickly.

- **Compact format, fits in a trousers pocket.**
- **Three lighting option including a focussable spotlight with a reflector lens in the lamp head.**
- **Battery status indicator.**
- **Integral magnet for easy attachment to metal surfaces (such as to steel girders or motors).**
- **Tipping mechanism permits flexible alignment for optimum illumination of the working area.**

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

ATEX zone: no

Illumination: 75 - 150 lm

Working life: 2 - 4 h

CRI value: 80

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

## Technical description

Weight	72 g
Working life	2 - 4 h
CRI value	80
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Overall height	157 mm
IP Index of Protection	IP 54
Battery voltage	3.7 V
Number of rechargeable batteries contained	1
Illumination	75 - 150 lm
ATEX zone	no
Overall length	27 mm
Bulb	LED module
Overall width	20 mm
Colour temperature	5400 - 6600 K
Battery capacity	0.75 A·h
Manufacturer's designation	iW4R
Type of product	Flashlight