

**Wet and dry vacuum cleaner ATTIX, Manufacturer's designation: 751-11****Order data**

Order number	078541 751-11
GTIN	4005337064141
Item class	07C

Description**Version:**

Robust and powerful **wet / dry vacuum cleaners** with flexible hose connection system (MultiFit) and for performing a very wide variety of professional cleaning tasks. **Degree of separation > 99.9%**.

- **Extremely quiet industrial vacuum cleaners with long-lasting washable PET fleece filter.**
- **Soft start, generous tool storage, and additional power tool socket.**

Supplied with:

Supplied with suction hose, curved hand tube, wet filter and washable filter element (PET), hose storage, and cable storage. Supplied with curved stainless steel hand tube, rubber oblique-end nozzle, **without drain hose**.

Note:

Other safety vacuum cleaners for all hazard classes (health hazard or explosive dusts) are available on request (class L, M, H).

Technical description

Suction hose length	4 m
Width	580 mm

Manufacturer's designation	ATTIX 751-11
Length	605 mm
Number of turbines	1
Air flow volume	60 l/s
Cable length	7.5 m
Hose Ø	36 mm
Container volume	70 l
Weight	25 kg
Operating noise	57 dB(A)
Power consumption	1500 W
Vacuum	230 mbar
Degree of separation	99.9 %
Height	970 mm
Special features	Extremely quiet
Filter system	PET fleece filter
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

Accessories

Rubber oblique-end nozzle Manufacturer's designation 7868	078546 7868
Floor nozzle, 400 mm wide Manufacturer's designation 3666	078555 3666
Workshop set Manufacturer's designation ATTIX5	078543 ATTIX5
Filter bag set 5 pieces suitable for vacuum cleaner type 751	078549 751
Chip basket Manufacturer's designation ATTIX7	078544 ATTIX7
Spare filter suitable for vacuum cleaner type 751	078548 751
Chip suction hose set Manufacturer's designation DN50	078545 DN50

Stainless steel extension tube Manufacturer's designation
8074

078556 8074

Joint nozzle Manufacturer's designation 7102

078547 7102