

## PRYOR

**Numeral letter punch set, 27 pieces Normal script A – Z, &, Character height: 3mm**



### Order data

Order number	085430 3
GTIN	5022044002081
Item class	08W

### Description

#### Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

**High performance precision punches**, chemically nickel-plated, very long service life.

**Normal script**; i. e. the punched character can be read directly on the component.

#### Application:

For punching into materials with a **strength up to 1200 N/mm<sup>2</sup>**.

#### Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

#### Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

### Technical description

overall length	63.5 mm
Shank thickness	6.35

Character height	3 mm
Type of product	Hand punch

## Accessories

Letter punch – individualNormal script A – Z Character height / Characters 3/G mm	085431 3/G
Letter punch – individualNormal script A – Z Character height / Characters 3/C mm	085431 3/C
Letter punch – individualNormal script A – Z Character height / Characters 3/O mm	085431 3/O
Letter punch – individualNormal script A – Z Character height / Characters 3/E mm	085431 3/E
Letter punch – individualNormal script A – Z Character height / Characters 3/A mm	085431 3/A
Letter punch – individualNormal script A – Z Character height / Characters 3/H mm	085431 3/H
Letter punch – individualNormal script A – Z Character height / Characters 3/B mm	085431 3/B
Letter punch – individualNormal script A – Z Character height / Characters 3/W mm	085431 3/W
Letter punch – individualNormal script A – Z Character height / Characters 3/N mm	085431 3/N
Letter punch – individualNormal script A – Z Character height / Characters 3/I mm	085431 3/I
Letter punch – individualNormal script A – Z Character height / Characters 3/X mm	085431 3/X
Letter punch – individualNormal script A – Z Character height / Characters 3/S mm	085431 3/S
Letter punch – individualNormal script A – Z Character height / Characters 3/J mm	085431 3/J
Letter punch – individualNormal script A – Z Character height / Characters 3/D mm	085431 3/D

Letter punch – individualNormal script A – Z Character height / Characters 3/M mm	085431 3/M
Letter punch – individualNormal script A – Z Character height / Characters 3/Y mm	085431 3/Y
Letter punch – individualNormal script A – Z Character height / Characters 3/Z mm	085431 3/Z
Letter punch – individualNormal script A – Z Character height / Characters 3/R mm	085431 3/R
Letter punch – individualNormal script A – Z Character height / Characters 3/U mm	085431 3/U
Letter punch – individualNormal script A – Z Character height / Characters 3/V mm	085431 3/V
Letter punch – individualNormal script A – Z Character height / Characters 3/K mm	085431 3/K
Letter punch – individualNormal script A – Z Character height / Characters 3/T mm	085431 3/T
Letter punch – individualNormal script A – Z Character height / Characters 3/P mm	085431 3/P
Letter punch – individualNormal script A – Z Character height / Characters 3/L mm	085431 3/L
Punch holder Type GRIP	085475 GRIP
Letter punch – individualNormal script A – Z Character height / Characters 3/F mm	085431 3/F
Letter punch – individualNormal script A – Z Character height / Characters 3/Q mm	085431 3/Q
Letter punch – individualNormal script A – Z Character height / Characters 3/& mm	085431 3/&