

DYMO
Labelling machine, Type: LM280

Order data

Order number	085500 LM280
GTIN	3501170968925
Item class	08U

Description
Version:

Robust portable labelling machines for fast and simple production of self-adhesive plastic labels. Permanent thermal transfer printing. Adjustable tape advance and reverse. Power supply from rechargeable **Li-ion battery**, mains charger. Simple text generation with quick-access buttons. Standard LabelManager™ 280 for office and home use with additional editing facilities on PC / Mac via USB port.

Application:

The labels stick to nearly all smooth grease-free surfaces.

Supplied with:

Includes lettering tape black on white and user instructions.

Note:

- **Different language versions can be installed.**
- **With German QWERTZ keyboard ex stock, French AZERTY keyboard available on a short lead time.**

Technical description

Print colour	black
Number of lettering styles	6

Keyboard layout	QWERTY
Length	206 mm
Tape cut-off type	manual
Number of visible characters in the display	2×14
Number of text lines	2
Type	LM280
available tape widths	6; 9; 12 mm
Number of available characters/symbols	220
suitable tape cartridge	D1
Number of font sizes	3
Mains adaptor	including
Width	108 mm
maximum character height	8.1 mm
Number of font widths	2
Special features	USB
Weight including rechargeable battery	395 g
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Height	41 mm
Power supply	Rechargeable battery-powered
Manufacturer's designation	Dymo 280
Type of product	Labelling machine

Accessories

Printer ribbon cartridge 19 mm×7 m polyester Type W	085550 W
Printer ribbon cartridge 12 mm×7 m polyester Type T	085520 T
Printer ribbon cartridge 19 mm×7 m polyester Type T	085550 T
Printer ribbon cartridge 12 mm×7 m polyester Type R	085520 R

Printer ribbon cartridge 12 mm×7 m polyester Type W	085520 W
Printer ribbon cartridge 19 mm×3.5 m nylon Type W	085516 W
Printer ribbon cartridge 9 mm×7 m polyester Type Y	085540 Y
Printer ribbon cartridge 24 mm×7 m polyester Type W	085560 W
Printer ribbon cartridge 19 mm×7 m polyester Type Y	085550 Y
Printer ribbon cartridge 24 mm×7 m polyester Type R	085560 R
Printer ribbon cartridge 9 mm×7 m polyester Type W	085540 W
Printer ribbon cartridge 19 mm×7 m polyester Type R	085550 R
Printer ribbon cartridge 6 mm×7 m polyester Type W	085530 W
Printer ribbon cartridge 24 mm×7 m polyester Type Y	085560 Y
Printer ribbon cartridge 12 mm×7 m polyester Type Y	085520 Y