

**Garant****Boring bar stabiliser 3×D midi, Type: 10R****Order data**

Order number	319456 10R
GTIN	4062406309114
Item class	31V

**Description****Version:**

Base body of high-quality tool steel, surface and functional faces hardened.

**Advantage:**

Reduces oscillation and vibration when used with all types of boring bars.

**Suitable for:**

All popular boring bars.

**Note:**

To determine the right type of boring bar stabiliser, it is essential to perform a collision check using the Hoffmann e-Tool data from the eShop or via the ToolScout! We recommend a maximum overhang length of 3×D of the types of boring bar used.

Maximum overhang, stabiliser incl. boring bar 6×D.

Boring bar stabiliser with 7×D or shank Ø D<sub>2</sub> = 25 mm available on request.

**Technical description**

Offset Z to the axis	11 mm
Overhang L <sub>1</sub>	30 mm
Shank Ø D <sub>2</sub>	32 mm
Ø D <sub>3</sub>	40 mm
Overall length L <sub>2</sub>	89 mm
Clamping Ø D <sub>1</sub>	10 mm

Shank length $L_s$	53 mm
Cutting direction	right-hand
Radius R	1.2 mm
C	1 mm
Boring depth up to	3×D
Vibration	damped
Type of product	Boring bar stabiliser