

PRYOR

Numeral letter punch set, 27 pieces Normal script A – Z, &, Character height: 4mm



Order data

Order number	085430 4
GTIN	5022044002524
Item class	08W

Description

Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

High performance precision punches, chemically nickel-plated, very long service life.

Normal script; i. e. the punched character can be read directly on the component.

Application:

For punching into materials with a **strength up to 1200 N/mm²**.

Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

Technical description

overall length	70 mm
Shank thickness	9.5

Character height	4 mm
Type of product	Hand punch

Accessories

Letter punch – individual Normal script A – Z Character height / Characters 4/W mm	085431 4/W
Letter punch – individual Normal script A – Z Character height / Characters 4/E mm	085431 4/E
Letter punch – individual Normal script A – Z Character height / Characters 4/L mm	085431 4/L
Letter punch – individual Normal script A – Z Character height / Characters 4/U mm	085431 4/U
Letter punch – individual Normal script A – Z Character height / Characters 4/D mm	085431 4/D
Letter punch – individual Normal script A – Z Character height / Characters 4/A mm	085431 4/A
Letter punch – individual Normal script A – Z Character height / Characters 4/M mm	085431 4/M
Letter punch – individual Normal script A – Z Character height / Characters 4/H mm	085431 4/H
Letter punch – individual Normal script A – Z Character height / Characters 4/P mm	085431 4/P
Letter punch – individual Normal script A – Z Character height / Characters 4/Y mm	085431 4/Y
Letter punch – individual Normal script A – Z Character height / Characters 4/V mm	085431 4/V
Letter punch – individual Normal script A – Z Character height / Characters 4/N mm	085431 4/N
Letter punch – individual Normal script A – Z Character height / Characters 4/G mm	085431 4/G
Letter punch – individual Normal script A – Z Character height / Characters 4/B mm	085431 4/B

Letter punch – individualNormal script A – Z Character height / Characters 4/Z mm	085431 4/Z
Letter punch – individualNormal script A – Z Character height / Characters 4/& mm	085431 4/&
Letter punch – individualNormal script A – Z Character height / Characters 4/l mm	085431 4/l
Letter punch – individualNormal script A – Z Character height / Characters 4/F mm	085431 4/F
Letter punch – individualNormal script A – Z Character height / Characters 4/X mm	085431 4/X
Punch holder Type GRIP	085475 GRIP
Letter punch – individualNormal script A – Z Character height / Characters 4/O mm	085431 4/O
Letter punch – individualNormal script A – Z Character height / Characters 4/K mm	085431 4/K
Letter punch – individualNormal script A – Z Character height / Characters 4/R mm	085431 4/R
Letter punch – individualNormal script A – Z Character height / Characters 4/Q mm	085431 4/Q
Letter punch – individualNormal script A – Z Character height / Characters 4/S mm	085431 4/S
Letter punch – individualNormal script A – Z Character height / Characters 4/T mm	085431 4/T
Letter punch – individualNormal script A – Z Character height / Characters 4/C mm	085431 4/C
Letter punch – individualNormal script A – Z Character height / Characters 4/J mm	085431 4/J