



Pneumatic ratchet screwdriver, Type: W2630



Order data

Order number	079121 W2630
GTIN	7322590034153
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal \emptyset . Reversible ratchet screwdriver with speed control in a compact design with glass-fibre composite casing for good thermal insulation. Exhaust air outlet can be rotated 360°.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Operating noise	86 dB(A)
maximum screw \emptyset (8.8 - 12.9)	M14
Manufacturer's designation	W2630
recommended hose size (internal \emptyset)	10 mm
Length	307 mm
Tool arbor size	1/2 in
Torque range	25 - 80 Nm
maximum air consumption	660 l/min

maximum speed	200 min ⁻¹
Weight	1.2 kg
maximum vibration to EN	10.5 m/s ²
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver